



FAST FLOOR 38-DH MEZZANINE FLOOR BOARD

Table showing the uniform distributed load (UDL) with various deflections.

Max support distance C-C	Span / 200 (deflection)	Span / 300 (deflection)	Span / 400 (deflection)
inch	lbs/SF	lbs/SF	lbs/SF
33.5	245.0	184.0	132.9
35.4	210.5	151.2	106.3
37.4	177.8	124.7	85.8
39.4	149.2	102.2	75.6
41.3	130.8	87.9	65.4
43.3	114.4	75.6	57.2
45.3	98.1	67.4	49
47	87.9	57.2	42.9
49	79.7	51.1	38.8
51	69.5	47.0	34.7
53	61.3	40.9	30.7
55	57.2	36.8	26.6
57	49.0	32.7	24.5
59	45.0	30.7	22.5

Bergvik North America, Inc., 212 West Main Street,
Suite 202-B, Salisbury, MD 21801
Tel: (410) 548 1449, Fax: (410) 548 2630.
Email: peter.brandstrom@bergvik.com Web: www.bergvik.com